


PQ CORES



PART NO.	DIMENSIONS (mm)								EFFECTIVE PARAMETER			Weight per set (g) Approx.	A _L ^{+30%} _{-20%}			
	A	B	C	D	E	F	G	H	Le(mm)	Ae(mm ²)	Ve(mm ³)		KM22	KM21	KM7	KM10
PQ20/16	20.90-21.70	17.60-18.40	12.0 min	8.00-8.20	5.00-5.30	8.60-9.00	13.60-14.40	7.90 min	37.6	61.9	2330	13	3600	3080		
PQ20/20	20.90-21.70	17.60-18.40	12.0 min	10.00-10.20	7.00-7.30	8.60-9.00	13.60-14.40	7.90 min	45.7	62.6	2850	16	3150	2650		
PQ26/20	26.84-27.76	22.04-22.96	15.5 min	9.97-10.23	5.60-5.90	11.80-12.20	18.55-19.45	10.50 min	45.0	121	5470	30	6200	5200		
PQ26/25	26.84-27.76	22.04-22.96	15.5 min	12.22-12.48	7.90-8.20	11.80-12.20	18.55-19.45	10.50 min	54.3	120	6530	36	5250	4390		
PQ32/20	32.50-33.50	27.00-28.00	19.0 min	10.17-10.43	5.60-5.90	13.25-13.75	21.50-22.50	19.00 min	55.9	169	9440	43	6800	6000		
PQ32/30	32.50-33.50	27.00-28.00	19.0 min	15.02-15.28	10.50-10.80	13.25-13.75	21.50-22.50	11.60 min	74.7	167	12500	57	5600	4580		
PQ35/35	35.50-36.70	31.50-32.50	23.5 min	17.22-17.48	12.35-12.65	14.15-14.65	25.50-26.50	11.80 min	86.1	190	16300	73	5200	4570		
PQ40/40	40.60-42.40	36.40-37.60	28.0 min	19.75-20.10	14.50-15.00	14.60-15.20	27.40-28.60	15.00 min	102.0	210	20500	97	4900	4100		
PQ50/50	50.40-51.70	43.30-44.70	32.0 min	24.70-25.30	17.70-18.40	19.65-20.35	31.40-32.60	18.00 min	26.00	43.00	1120	36.10	7400	6150		